

SE-1/SE-3

Single/Three-channel ECG

Mounting Solutions ➤



Specification

	SE-1	SE-3
Input Circuit	Defibrillation protection	
Lead	Standard 12 leads	
Acquisition Mode	Single lead	12 leads simultaneous acquisition
A/D Converter	12 bits	12 bits/24 bits (optional)
Input Voltage Range	<±5mVpp	
Calibration Voltage	1mV ±3%	
Frequency Response	0.05Hz~150Hz (-3dB)	
Input Impedance	≥50Ω (10Hz)	
Input Circuit Current	≤0.05μA	
DC Offset Voltage	±300mV	±500mV/±600mV (optional)
Noise	≤12.5μVp-p	
Time Constant	≤3.2s	
DC Offset Voltage	±300mV	
Baseline Adjustment	Automatic	
Filter	EMG Filter: 35Hz (-3dB) AC/DFT Filter: 50Hz/60Hz (-20dB)	AC Filter: On/Off DFT Filter: 0.05Hz/0.15Hz/0.25Hz/0.32Hz/0.5Hz/0.6Hz EMG Filter: 25Hz/35Hz/45Hz/OFF LOWPASS Filter: 150Hz/100Hz/75Hz
CMRR	≥110dB	≥5100dB/≥115dB (optional)
Recording Mode	Auto: 1CH, 1CH+1R Manual: 1CH	Auto: 3CH, 3/2CH, 3CH+1R, 1CH, 1CH+1R Manual: 3CH, 3/2CH, 1CH Rhythm: Single rhythm lead
Rhythm Lead	Any lead selectable	
Power Supply	AC: 100V-115V/220V-240V, 50/60Hz Built-in rechargeable Li-ion battery: Rated voltage: 14.8V More than 3 hrs continuous recording under battery supply	
Recorder	Thermal printer	Thermal printer/External printer
Record Paper	50mmx30m	80mm x 20m
Paper Speed	25mm/s, 50mm/s	5mm/s, 6.25mm/s, 10mm/s, 12.5mm/s, 25mm/s, 50mm/s (±3%)
Dimension	288mm x 210mm x 70mm	
Weight	2.3 kg	2.5kg
Display	192 x 64 dots single color LCD screen	320x240 dots single color LCD Screen 192x64 dots single color LC Screen
Communication Interface	N/A	Ethernet/RS232/USB

EDANUSA
www.edanusa.com

SE-1/SE-3

Single/Three-channel ECG



To Purchase, Visit Avobus.com or call [1-800-674-3655](tel:1-800-674-3655)

4204 Jutland Drive,
Suite B, San Diego, CA 92117
Toll Free Phone Number:
888.850.4597

Care for Health

SE-3 Series

Three-channel ECG



SE-3 (Wide Screen)

Portable & User-friendly Design

- Foldable LCD screen, vivid waveform display
- Built-in rechargeable Li-ion battery, AC/DC power supply
- Communication interface: Ethernet/RS232/USB

Streamlined Workflow

- One-button operation
- Auto/Manual/Rhythm work mode
- Automatic baseline adjustment
- Lead-off detection and alarm

Accurate Clinical Performances

- 12 leads simultaneous acquisition with 24 bits A/D converter optional
- Automatic ECG measurements and interpretation tested by CSE/AHA/MIT database
- Complete digital filtering, resisting baseline drift, AC and EMG interference



Foldable Screen



Portable Design
(Handle Optional)



One-button Operation



Flexible Printing Solutions

- Built-in high-resolution thermal printer
- 12 leads grid printing on normal A4 paper by external printer


Data Management

- Large patient data storage: 120 ECGs (Narrow Screen), 144 ECGs (Wide Screen), which can be enlarged by a USB flash disk
- PC-based ECG data management software (optional)




SE-3 (Narrow Screen)

PC-based ECG Data Management Software



Smart ECG Viewer

Intuitive interface to improve your work efficiency



SE-1 Single-channel ECG

- Vivid waveform with foldable LCD display
- Built-in high resolution thermal printer
- Built-in rechargeable Li-ion battery, AC/DC power supply
- Well designed membrane keyboard

- Digital filtering, resisting baseline drift, AC and EMG interference
- Automatic baseline adjustment
- Auto/Manual work mode
- Lead-off detection and alarm

To Purchase, Visit Avobus.com or call [1-800-674-3655](tel:1-800-674-3655)